
by Fritz Ruoss

FED2+, FED3+: Compare spring material

As in FED1 +, you can now choose the optimal material for tension springs and torsion springs by comparing the materials from the database.

Select the material with a mouse click or the cursor keys, then the spring is recalculated and the results are displayed in the background graphic. In the table you can compare the materials based on the safety factors S k2 = tauz / tauk2 and S kh = tauhz / (tauk2-tauk1).




WL1 +: Calculation of shafts on three, four or five bearings

The calculation of shafts with three, four or five bearings now runs faster and the message "Final value C not reached" no longer appears because the accuracy was limited to a minimum of 0.0001mm. This mainly applies to shafts with zero deflection in either xy plane or xz plane.

LG1: Axial needle roller and cage assemblies and axial cylindrical roller bearings

H	ı	▶ ▶I	Search	Search Ne	ext 17 /106	OK.	Cancel			
NA	ME	DC1	D1	DC	KD1	T	DW	В	AR	EB
K8:	1110-TV	50	52	70	70	14	6	4	0,6	52
K8:	1210-TV	50	52	78	78	22	9	6,5	1	53
K85	9310-TV	50	52	95	95	27	8	9,5	1,1	56
K8:	1111-TV	55	57	78	78	16	6	5	0,6	57
K8:	1211-TV	55	57	90	90	25	11	7	1	59
K8	9311-TV	55	57	105	105	30	9	10,5	1,1	61
K8:	1112-TV	60	62	85	85	17	7,5	4,8	1	62
K8:	1212-TV	60	62	95	95	26	11	7,5	1	64
K8	9312-TV	60	62	110	110	30	9	10,5	1,1	66
K8	9412-TV	60	62	130	130	42	14	14	1,5	65
K8:	1113-TV	65	67	90	90	18	7,5	5,3	1	67
K8:	1213-TV	65	67	100	100	27	11	8	1	69
K8	9313-TV	65	67	115	115	30	9	10,5	1,1	71
K8	9413-TV	65	68	140	140	45	15	15	2	70
K8:	1114-TV	70	72	95	95	18	7,5	5,3	1	72
K8:	1214-TV	70	72	105	105	27	11	8	1	74
K8	9314-TV	70	72	125	125	34	10	12	1,1	76

With LG1 you can now also calculate axial bearings: Axial needle roller and cage assemblies and axial cylindrical roller bearings have been added.




ZAR5, ZAR7, ZAR8: Tooth gap drawing button at input of measuring circle

ZAR5 No. of teeth measured, Ball and pin diameters						
gear S No. of teeth measured k 2	gear P gear H					
Ball and pin diameters DM 3,1	3,4 2,6 mm < ?					
Gap S + DM	Gap P + DM Gap H + DM					
OK Cancel Help	mm <> inch Calc					


At "Edit Measurement", a push of the new buttons "Gap" shows a drawing of the tooth gap with measuring circle in the background window for sun gear S, planet gear P, ring gear H.

ZAR7 No. of teeth measured, Ball and pin diameters							
No. of teeth measured k	gear S	gear Pi	gear Pe	gear H	< ?		
Ball and pin diameters DM	5,1 Gap S	6 Gap Pi	6,2 Gap Pe	5 Gap H	mm < ?		
OK Cancel I	Help		mm <>		Calc		

So you can quickly test different ball or pin diameters for suitability.



SR1/SR1+: Elastic resilience: consider multiple bore diameters and long holes



Under "Calculation method" you can now configure "di deformation cone" to calculate the hole in the clamping plates as a cone instead of a cylinder in the case of elastic resilience. If you use clamping plates with standard-compliant bores, this is of no interest, the result always remains the same. The elastic resilience deltaP only changes if several clamping plates with changing inside diameters or elongated holes are used. Instead of the inner diameter of the clamping plate, a cone from the inner contact diameters of the adjacent clamping plates is then used.


The elastic compliance is calculated as follows:

Cylinder: Delta = $L / (E * A) = 4 * L / (E * pi * d^2)$

Truncated cone: Delta = 4 * L * (1 / dmin - 1 / dmax) / (pi * E * (dmax-dmin))

With L = length, d = diameter, E = modulus of elasticity

If this option is selected, the inner cones are drawn in the drawing of the bolted joint.




SR1 Tip: Tightening angle for combined torque-and-angle controlled tightening

SR1 calculates the tightening angle from the elastic origin to the specified yield strength factor. For example, torque-controlled tightening up to 30% yield point, then further up to 90% yield point under rotation angle control. How large is the angle of rotation from 30% yield point to 90% yield point? Quite simply, SR1 calculates the tightening angle of rotation alphaRe up to the yield point. Then the angle of further rotation is

deltaAlpha = alphaRe * (90% -30%) / 100% = 0.6 * alphaRe

The tightening torque for 30% Re can either be entered, or read off in the M-alpha diagram for alpha = 0.3 * alphaRe (with deviation due to friction tolerance).



Tip: Bending angle and deflection of leaf springs, girders and shafts

The deflection of leaf springs firmly clamped on one side is calculated with:

$$s = F * L^3 / (2 * E * I)$$

the bending angle at the free end with

 $tan (alpha) = F * L^2 / (2 * E * I)$

So is

tan (alpha) = 3/2 * s / L

Or the other way around

s = 2/3 * tan (alpha) * L

Independent of the spring width, thickness, material.

Example: If the incline of a 100 mm long leaf spring should not exceed 15 $^{\circ}$, the deflection must be less than 17.8 mm.

Grüß Gott im Länd

The green state government of Baden-Württemberg wants to lure people into the state in a ridiculous, multi-million dollar advertising campaign "Welcome to the Länd" in the middle of Corona times. More travelers, more traffic, more CO2, more pollutants, more traffic jams, more corona. No problem for the GrändPä of the Länd. The main thing is that people are vaccinated. Unvaccinated people are not welcome, as accommodation is prohibited. And those who do not immediately disappear will be forcibly vaccinated.

Corona calculations: RKI weekly report from 2021-12-02:

(Table 3, breakthroughs in vaccination, mean 44-47, age 12-99 "cumulative")

Hospitalized COVID-19 cases: 11062, of which vaccinated: 4870, therefore unvaccinated: 6192 Covid-19 cases in intensive care unit: 1721, of which vaccinated: 592, therefore unvaccinated: 1129

Deceased COVID-19 cases: 1441, of which vaccinated: 665, therefore unvaccinated: 776

Calculations:

1129/1721 = 66% of the COVID-19 admissions to the intensive care unit were unvaccinated.

Of the 1129 unvaccinated people in the intensive care unit, 665/1129 = 59% died.

Of the 529 people vaccinated in the intensive care unit, all died (665> 592).

Corona extrapolation with 100% vaccination quota from RKI weekly report of 2021-12-02

With a vaccination rate of 100% there are no more unvaccinated people, but 30/70 = 43% more vaccinated people and correspondingly 43% more vaccination breakthroughs:

Hospitalized COVID-19 cases: 6964, all vaccinated (4870 + 43%)

COVID-19 cases in intensive care: 775, all vaccinated (592 + 43%)

Deceased COVID-19 cases: 951, all vaccinated (665 + 43%)

Calculations: With a vaccination rate of 100%, there is 37% less hospitalization, 55% fewer Covid intensive care patients, 34% fewer deaths.

Vaccination champion: compulsory vaccination does not protect against corona waves

The vaccination world champion Portugal (vaccination rate 98% for over 12-year-olds) had a new-infection incidence of 275 on December 14th, 2021, which is only 20% less than in Germany. A vaccination does not protect against a fifth wave and certainly not against new mutations. After all, the omicron variant was spread all over the world by vaccinated air travelers. Nevertheless, one can now advise vaccination: on the one hand, many millions of people have been vaccinated for many months without hearing too much about serious side effects and vaccination victims. On the other hand, with the high number of new infections, it is hardly possible to avoid contact with infected people. But compulsory vaccination? Sounds like Adolf H. Can't Olaf S. think of anything better? Suggestion: Unvaccinated people have to apply and pay for an additional corona risk health insurance. This pays if these people need intensive care with Covid. Otherwise they will be turned away at the hospital or taken to the palliative care unit. A compulsory vaccination, on the other hand, would be clumsy and unimaginative. It is embarrassing if not even enough vaccine is available for all those willing for the 3rd vaccination (booster) and 4th vaccination (Omikron).

Corona contamination theory

In India the 7-day incidence has dropped to 5, even though only 37% of the population are vaccinated. How come Corona in India was short and violent. Within a short time there were tons of corona infections and many deaths. Antibody tests in New Delhi have now shown that 97% of the population had formed antibodies against Covid, according to which almost everyone came into contact with the virus and survived an infection unnoticed.

Worldwide, new corona mutations are displacing the previously prevalent corona viruses if they are more contagious than those. More deadly mutations die with their host. So we hope for new corona mutations that are more contagious than the previous ones, but harmless in their course.

And until then: Vaccinated people can be boosted, those who have not been vaccinated can be vaccinated and / or avoid contact, eat healthily, exercise in the fresh air. Stay healthy!

HEXAGON PRICE LIST 2022-01-01

Base price for single licences (perpetual)	EUR
DI1 Version 2.1 O-Ring Seal Software	190
DXF-Manager Version 9.1	383
DXFPLOT V 3.2	123
FED1+ V31.3 Helical Compression Springs incl. spring database, animation, relax., 3D,	695
FED2+ V22.0 Helical Extension Springs incl. Spring database, animation, relaxation,	675
FED3+ V21.5 Helical Torsion Springs incl. prod.drawing, animation, 3D, rectang.wire,	600
FED4 Version 8.0 Disk Springs	430
FED5 Version 17.0 Conical Compression Springs	741
FED6 Version 18.0 Nonlinear Cylindrical Compression Springs	634
FED7 Version 15.0 Nonlinear Compression Springs	660
FED8 Version 7.4 Torsion Bar	317
FED9 Version 7.0 Spiral Spring	394
FED9+ Version 7.0 Spiral Spring incl. production drawing, animation, Quick input	490
FED10 Version 4.5 Leaf Spring	500
FED11 Version 3.6 Spring Lock and Bushing	210
FED12 Version 2.7 Elastomer Compression Spring	220
FED13 Version 4.2 Wave Spring Washers	228
FED14 Version 2.6 Helical Wave Spring	395
FED15 Version 1.6 Leaf Spring (simple)	180
FED16 Version 1.3 Constant Force Spring	225
FED17 Version 2.1 Magazine Spring	725
GEO1+ V7.5 Cross Section Calculation incl. profile database	294
GEO2 V3.3 Rotation Bodies	194
GEO3 V4.0 Hertzian Pressure	205
GEO4 V5.3 Cam Software	265
GEO5 V1.0 Geneva Drive Mechanism Software	218
GEO6 V1.0 Pinch Roll Overrunning Clutch Software	232
GEO7 V1.0 Internal Geneva Drive Mechanism Software	219
GR1 V2.2 Gear construction kit software	185
GR2 V1.2 Eccentric Gear software	550,-
HPGL-Manager Version 9.1	383
LG1 V7.0 Roll-Contact Bearings	296
LG2 V3.1 Hydrodynamic Plain Journal Bearings	460
SR1 V24.1 Bolted Joint Design	640
SR1+ V24.1 Bolted Joint Design incl. Flange calculation	750
TOL1 V12.0 Tolerance Analysis	506
TOL2 Version 4.1 Tolerance Analysis	495
TOLPASS V4.1 Library for ISO tolerances	107
TR1 V6.4 Girder Calculation WL1+ V21.7 Shaft Calculation incl. Roll-contact Bearings	757
WN1 V12.4 Cylindrical and Conical Press Fits	945 485
WN2 V11.2 Involute Splines to DIN 5480	250
WN2+ V11.2 Involute Splines to DIN 5480 and non-standard involute splines	380
WN3 V 6.0 Parallel Key Joints to DIN 6885, ANSI B17.1, DIN 6892	245
WN4 V 6.1 Involute Splines to ANSI B 92.1	276
WN5 V 6.1 Involute Splines to ISO 4156 and ANSI B 92.2 M	255
WN6 V 4.1 Polygon Profiles P3G to DIN 32711	180
WN7 V 4.1 Polygon Profiles P4C to DIN 32712	175
WN8 V 2.6 Serration to DIN 5481	195
WN9 V 2.4 Spline Shafts to DIN ISO 14	170
WN10 V 4.4 Involute Splines to DIN 5482	260
WN11 V 2.0 Woodruff Key Joints	240
WN12 V 1.2 Face Splines	256
WN13 V 1.0 Polygon Profiles PnG	238
WN14 V 1.0 Polygon Profiles PnC	236
WNXE V 2.3 Involute Splines – dimensions, graphic, measure	375
WNXK V 2.2 Serration Splines – dimensions, graphic, measure	230
WST1 V 10.2 Material Database	235
ZAR1+ V 26.7 Spur and Helical Gears	1115
zon open ene rionoar obaro	1110.

ZAR2 V8.2 Spiral Bevel Gears to Klingelnberg	792
ZAR3+ V10.4 Cylindrical Worm Gears	620
ZAR4 V6.3 Non-circular Spur Gears	1610
ZAR5 V12.4 Planetary Gears	1355
ZAR6 V4.3 Straight/Helical/Spiral Bevel Gears	585
ZAR7 V2.3 Plus Planetary Gears	1380
ZAR8 V1.9 Ravigneaux Planetary Gears	1950
ZAR9 V1.0 Cross-Helical Screw Gears	650
ZARXP V2.6 Involute Profiles - dimensions, graphic, measure	275
ZAR1W V2.6 Gear Wheel Dimensions, tolerances, measure	450
ZM1.V3.0 Chain Gear Design	326
ZM2.V1.0 Pin Rack Drive Design	320
ZM3.V1.0 Synchronous Belt Drive Design	224

PACKAGES	EUR
HEXAGON Mechanical Engineering Package (TOL1, ZAR1+, ZAR2, ZAR3+, ZAR5, ZAR6, WL1+, WN1,	
WN2+, WN3, WST1, SR1+, FED1+, FED2+, FED3+, FED4, ZARXP, TOLPASS, LG1, DXFPLOT, GEO1+,	8,500
TOL2, GEO2, GEO3, ZM1, ZM3, WN6, WN7, LG2, FED12, FED13, WN8, WN9, WN11, DI1, FED15, GR1)	
HEXAGON Mechanical Engineering Base Package (ZAR1+, ZAR3+, ZAR5, ZAR6, WL1+, WN1, WST1,	4,900
SR1+, FED1,+, FED2+, FED3+)	4,900
HEXAGON Spur Gear Package (ZAR1+ and ZAR5)	1,585
HEXAGON Planetary Gear Package (ZAR1+, ZAR5, ZAR7, ZAR8, GR1)	3,600
HEXAGON Involute Spline Package (WN2+, WN4, WN5, WN10, WNXE)	1,200
HEXAGON Graphic Package (DXF-Manager, HPGL-Manager, DXFPLOT)	741
HEXAGON Helical Spring Package (FED1+, FED2+, FED3+, FED5, FED6, FED7)	2,550
HEXAGON Complete Spring Package (FED1+, FED2+, FED3+, FED4, FED5, FED6, FED7, FED8,	4,985
FED9+, FED10, FED11, FED12, FED13, FED14,, FED15, FED16, FED17)	•
HEXAGON Tolerance Package (TOL1, TOL1CON, TOL2, TOLPASS)	945
HEXAGON Complete Package (All Programs)	14,950

Quantity Discount for Individual Licenses

Licenses	2	3	4	5	6	7	8	9	>9
Discount %	25%	27.5%	30%	32.5%	35%	37.5%	40%	42.5%	45%

Network Floating License

Licenses	1	2	3	4	5	6	78	911	>11
Discount/Add.cost	-50%	-20%	0%	10%	15%	20%	25%	30%	35%

(Negative Discount means additional cost)

Language Version:

- German and English: all Programs
- French: FED1+, FED2+, FED3+, FED4, FED5, FED6, FED7, FED9+, FED10, FED13, FED14, FED15, TOL1, TOL2.
- Italiano: FED1+, FED2+, FED3+, FED4, FED5, FED6, FED7, FED9+, FED13, FED14, FED17.
- Swedish: FED1+, FED2+, FED3+, FED5, FED6, FED7.
- Portugues: FED1+, FED17
- Spanish: FED1+, FED2+, FED3+, FED17

Updates:

opaatoo.		
Software Update	(software Win32/64 + pdf manual)	40 EUR
Software Undate	(software 64-bit Win + pdf manual)	50 FUR

Update Mechanical Engineering Package: 800 EUR, Update Complete Package: 1200 EUR **Maintenance contract** for free updates: annual fee: 150 EUR + 40 EUR per program

Hexagon Software Network Licenses

Floating License in the time-sharing manner by integrated license manager.

Conditions for delivery and payment

Delivery by Email or download (zip file, manual as pdf files): EUR 0.

General packaging and postage costs for delivery on CD-ROM: EUR 60, (EUR 25 inside Europe)

Conditions of payment: bank transfer in advance with 2% discount, or PayPal (paypal.me/hexagoninfo) net. After installation, software has to be released by key code. Key codes will be sent after receipt of payment.

E-Mail: info@hexagon.de

Web: www.hexagon.de